

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 5/S4mm

Order data

Order number	268718 5/S4
GTIN	4045197923769
Item class	21V

Technical description

Overhang L_1	15 mm
Insert size	4 mm
Centre offset L_3	2.95 mm
Clamping height L_2	4.6 mm
Pack of insert screws	269028 10
ISO code toolholder	A05X SCLDR/LS4
suitable indexable insert	CDCT S4010.
Minimum pre-drill $\varnothing D_{\min}$	5.78 mm
Overall length L	65 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	5 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200