

Garant
Boring bar, steel, left-hand, Shank \varnothing / insert size: 8/S4mm

Order data

Order number	268718 8/S4
GTIN	4045197923783
Item class	21V

Technical description

Pack of insert screws	269028 10
ISO code toolholder	A08X SCLDR/LS4
Clamping height L_2	7.49 mm
suitable indexable insert	CDCT S4010.
Setting angle κ	95 degrees
Overhang L_1	24 mm
Minimum pre-drill $\varnothing D_{\min}$	9.05 mm
Centre offset L_3	4.7 mm
Insert size	4 mm
Overall length L	76 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200