

**Garant**
**Adjustable spanner plug-in head, Type-Opening width: 2-30mm**

**Order data**

Order number	657850 2-30
GTIN	4045197592293
Item class	61E

**Description**
**Version:**

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Great versatility due to the adjustable opening width.

**Caution:**

Reference dimension correction necessary on the torque wrench (change to the setting value).

**Advantage:**

Adjustment of the opening width **does not necessitate modification of the reference dimension.**

**Material:**

Chrome vanadium steel, chrome-plated.

**Cutting dataa:**
**Legend for drawing and formula:**

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

$L$  = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

**Suitable for:**

Torque wrench with rectangular sockets.

**Note:**

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

---

**Technical description**

Width b	71.8 mm
Plug-in shank	14×18 mm
Height h	16.9 mm
Opening width	3/16 – 1.3/16 in
Opening width	5 - 30 mm
Pitch S	74.4 mm
Exchangeable tool	Plug-in head
Type of product	Open ended plug-in head