



Grooved water pump pliers, chrome-plated, overall length: 125 mm



Order data

Order number	705000 125
GTIN	4003773050490
Item class	73F

Description

Version:

The clamping pressure acts only on the **grooved sliding joint** which has multiple adjustment positions; hence no slipping and no wear on the screw. Designed to prevent fingers being trapped. Self-tightening on pipes and nuts. With notched serrated gripping jaws, induction hardened.

Pliers chrome-plated, plastic coated handles.

Standard:

DIN ISO 8976

Material:

Chrome vanadium steel, drop forged.

Hexagon across flats: 14 mm

Jaw capacity for pipes: 1 1/16 inch

Technical description

overall length	125 mm
Jaw capacity for pipes	1 1/16 inch
Hexagon across flats	14 mm
Handle	plastic coated
Surface	chrome-plated
Standard	DIN ISO 8976
Material	Chrome vanadium steel

non-sparking	no
Self-locking	yes
Protection against trapping fingers	yes
Type of product	Pipe wrench and water pump pliers

Accessories

Electronics tool kit, 118 pieces without case	680405
Electronics tool kit, 118 pieces with aluminium tool case	680400