



Ring plug-in head, Type-Width across flats: 1-8mm



Order data

Order number	657900 1-8
GTIN	4018754034062
Item class	63A

Description

Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Material:

Chrome alloy steel, non-flaking, chrome-plated over nickel.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Technical description

Width across flats	8 mm
Height h	8 mm
Plug-in shank	9×12 mm
Width b	14.2 mm
Series	732/10
Pitch S	17.5 mm
Exchangeable tool	Plug-in head
Tool with ratchet function	no
Type of product	Ring plug-in head