

Garant
Tap wrench, adjustable strengthened, Type: 4

Order data

Order number	148200 4
GTIN	4045197923974
Item class	11K

Description
Version:

With hardened jaws and steel grips. For use in confined spaces one steel handle can be unscrewed.

For **heavy** duties and **precision applications**. All dimensions with **high-quality forged steel base bodies** and integral fixed jaws. **Round vials** for straight application.

Standard: DIN 1814

Capacity □: 5.5 - 16 mm

for hand taps DIN 352: M9 – M27

for hand reamer Ø DIN 206: 7 - 20 mm

Overall length: 480 mm

Technical description

for hand reamer Ø DIN 206	7 - 20 mm
Overall length	480 mm
for hand taps DIN 352	M9 – M27
Capacity □	5.5 - 16 mm
Standard	DIN 1814
Type of product	Tap wrench