

**Water pump pliers with stepped fine adjustment, black, overall length: 180 mm****Order data**

Order number	706000 180
GTIN	4045197439536
Item class	71B

**Description****Version:**

Box joint (= double guides). Designed to prevent fingers being trapped. Push-button **fine step adjustment**. Concave profile serrated jaws, self-clamping. Surface manganese phosphated, polished jaws. Ergonomically shaped handles with non-slip plastic coating.

**Standard:**

**DIN ISO 8976**

**Material:**

Chrome vanadium steel, drop forged.

Hexagon across flats: 28 mm

Jaw capacity for pipes: 1 inch

Number of fine adjustment steps: 10

**Technical description**

Number of fine adjustment steps	10
overall length	180 mm
Jaw capacity for pipes	1 inch
Hexagon across flats	28 mm
Surface	manganese phosphated, polished jaws
Norm	DIN ISO 8976
Type of jaws	concave profile serrated jaws

Handle	non-slip plastic coating
Material	Chrome vanadium steel, drop forged
non-sparking	no
Stepped fine adjustment	yes
Self-locking	yes
Protection against trapping fingers	yes