



Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone hard, Cross-head size / overall length: 1/25mm



Order data

Order number	675380 1/25
GTIN	4013288191687
Item class	63H

Description

Version:

For use in manual drivers or machines with suitable hexagon holder or for use in adapters No. 675000 – 675050.

With torsion zone, **hard**. Ideal for light applications (e.g. screw driving into wood, plastic etc.)

Application:

For Phillips cross-head screws to DIN 3128 and DIN ISO 2351-2.

Standard:

DIN ISO 1173.

Material:

Chrome vanadium special alloy, **toughened**.

Technical description

Cross-head size	1
overall length	25 mm
Bit hexagon shank	C 6,3
Manufacturer's designation	855/1 TH PZ
Standard	DIN ISO 1173
Drive profile	Pozidriv screwdriver
Type of product	Bit tool

