



External micrometer Set, 3 pieces, Measuring range: 0-25mm



Order data

Order number	420403 0-25
GTIN	4045197925152
Item class	41B

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

With quick drive and ratchet on the barrel for one-hand use and use in the holder.

Supplied with:

3 x external micrometers No. 420402 size 0 – 25.

Technical description

Spindle Ø	6.5 mm
Micrometer barrel graduations	1/50 mm
Calibration	B1
Scale divisions	0.01 mm
Measuring range	0 - 25 mm
Barrel Ø	19 mm
Standard	DIN 863
Ratchet	yes

Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/420403-0-25>