



Wire twisting pliers, overall length: 230mm



Order data

Order number	707910 230
GTIN	4018754094677
Item class	73A

Description

Version:

Body drop-forged. Inner face of jaws serrated. Induction hardened cutting edges. **Front of teeth chamfered to 40°.**

Application:

For twisting locking wires (see diagram); by moving along any length can be worked. For wire \varnothing up to approx. 1.6 mm. For right-handed and left-handed action, with automatic return.

Material:

Special steel, burnished or painted finish, bright finished head.

Technical description

Jaw shape	40° chamfered
for wire \varnothing	<1.6 mm
overall length	230 mm
Jaw characteristics	Induction hardened cutting jaws
Type of jaws	Inner face of jaws roughened
Material	Special steel
Surface	burnished or varnished, bright finished head
Type of product	Wire twisting pliers

