



Water pump pliers Cobra® chrome-plated with coated handles, overall length: 300mm



Order data

| | |
|--------------|---------------|
| Order number | 705950 300 |
| GTIN | 4003773014126 |
| Item class | 73F |

Description

Version:

Box joint (= double guidance). Designed to prevent fingers being trapped. Concave profile serrated jaws, self-clamping.

Jaws chrome-plated, handles with multi-component covering. With **push-button fine step adjustment**.

Standard:

DIN ISO 8976

Material:

Chrome vanadium electro-steel, drop forged.

Optional extras:

Soft jaws No. 705805 size 180-300.

Technical description

| | |
|---------------------------------|--------------------------|
| Number of fine adjustment steps | 30 |
| overall length | 300 mm |
| Jaw capacity for pipes | 2.3/4 in |
| Hexagon across flats | 60 mm |
| Handle | Multi-component covering |
| Manufacturer's designation | Cobra |
| Surface | chrome-plated |

| | |
|-------------------------------------|-----------------------------------|
| Standard | DIN ISO 8976 |
| Material | Chrome vanadium steel |
| non-sparking | no |
| Quick adjustment | no |
| Self-locking | yes |
| Protection against trapping fingers | yes |
| Type of product | Pipe wrench and water pump pliers |

Accessories

| | |
|---------------------------------|------------|
| Spare parts assortment Type 300 | 705920 300 |
|---------------------------------|------------|