



## Wire twisting pliers, overall length: 280mm



### Order data

Order number	707910 280
GTIN	4018754094684
Item class	73A

### Description

#### Version:

Body drop-forged. Inner face of jaws serrated. Induction hardened cutting edges. **Front of teeth chamfered to 40°.**

#### Application:

For twisting locking wires (see diagram); by moving along any length can be worked. For wire Ø up to approx. 1.6 mm. For right-handed and left-handed action, with automatic return.

#### Material:

Special steel, burnished or painted finish, bright finished head.

### Technical description

overall length	280 mm
for wire Ø	<1.6 mm
Jaw shape	40° chamfered
Jaw characteristics	Induction hardened cutting jaws
Type of jaws	Inner face of jaws roughened
Material	Special steel
Surface	burnished or varnished, bright finished head
Type of product	Wire twisting pliers

