

**Wire twisting pliers, overall length: 230mm****Order data**

Order number	707920 230
GTIN	4045197593917
Item class	72B

Description**Version:**

Body drop-forged. Inner face of jaws serrated. Induction hardened cutting edges. **Front of teeth chamfered to 40°.**

Application:

For twisting locking wires (see diagram); by moving along any length can be worked. For wire \varnothing up to approx. 1.6 mm. For right-handed and left-handed action, with automatic return.

Material:

Special steel, burnished or painted finish, bright finished head.

Technical description

Jaw shape	40° chamfered
overall length	230 mm
for wire \varnothing	<1.6 mm
Jaw characteristics	Induction hardened cutting jaws
Type of jaws	Inner face of jaws roughened
Material	Special steel
Surface	burnished or varnished, bright finished head
Type of product	Wire twisting pliers

