

**Wire twisting pliers, overall length: 290mm****Order data**

| | |
|--------------|---------------|
| Order number | 707920 290 |
| GTIN | 4045197593924 |
| Item class | 72B |

Description**Version:**

Body drop-forged. Inner face of jaws serrated. Induction hardened cutting edges. **Front of teeth chamfered to 40°.**

Application:

For twisting locking wires (see diagram); by moving along any length can be worked. For wire \varnothing up to approx. 1.6 mm. For right-handed and left-handed action, with automatic return.

Material:

Special steel, burnished or painted finish, bright finished head.

Technical description

| | |
|------------------------|---|
| for wire \varnothing | <1.6 mm |
| Jaw shape | 40° chamfered |
| overall length | 290 mm |
| Jaw characteristics | Induction hardened cutting jaws |
| Type of jaws | Inner face of jaws roughened |
| Material | Special steel |
| Surface | burnished or varnished, bright finished head |
| Type of product | Wire twisting pliers |

