

**HOLEX®****Grip wrench PLUS with pivoted lower jaw, overall length: 250 mm****Order data**

Order number	708700 250
GTIN	4045197896018
Item class	76B

**Description****Version:**

Serrated jaws and sturdy spring steel body. Lower jaw with movable clamping face. **Parallel and prismatic clamping is available over the entire clamping range.** Fully nickel-plated.

**Application:**

Equally suitable for holding flat, profiled and round materials, clamping force up to 10,000 N.

**Material:**

Chrome vanadium steel gripping jaws, drop forged.

**Spare part:**

Spare spring No. 708300 size 250.

Jaw length: 45 mm

Jaw capacity for round and rectangular material: 45 mm

**Technical description**

overall length	250 mm
Jaw length	45 mm
Jaw capacity for round and rectangular material	45 mm

**Accessories**

Spring Type 250	708300 250
-----------------	------------