

**Electronic torque screwdriver, maximum torque: 50cNm****Order data**

| | |
|--------------|---------------|
| Order number | 659050 50 |
| GTIN | 4045197503862 |
| Item class | 62E |

Description**Version:**

Torque screwdriver with a flexible range of applications; with a 2-component handle, large display and quick-change coupling shank for bits. When the set value is reached, the torque screwdriver gives a clear visual and audible signal. 2 working modes are available - peak value display and tracking value display. Stores up to 50 values.

Units of measure: cNm, lbf·in, kgf·cm

Application:

Torque control; controlled tightening of screws in a single operation or for small batch production.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

| | |
|-------------------------------|-------------|
| Resolution | 0.1 cNm |
| Weight | 200 g |
| maximum torque | 50 cNm |
| Torque measuring accuracy | ±2 % |
| Torque range | 10 - 50 cNm |
| Number of batteries contained | 1 |
| Release signalling | optisk |

| | |
|---------------------------|-------------------------------------|
| Release signalling | akustisk |
| Connection format | Bit holder 1/4 inch |
| Reversible reading | cNm |
| Reversible reading | lbf·in |
| Reversible reading | kgf·cm |
| Measurement process | Torque |
| Trigger principle | Electromechanical trigger |
| Feedback | displaying |
| Setting the trigger value | digital, adjustable |
| Adjustable trigger value | adjustable |
| Overall length L | 203 mm |
| Display | digital |
| Calibration | O3 |
| Direction of tightening | For right- and left-hand tightening |
| Test certificate | Manufacturer's test certificate |
| Bit socket | F 6.3 |
| Standard | DIN EN ISO 6789 |
| Data can be recorded | yes |
| Measurement technology | electronic |
| Battery type | LR3 |
| Power supply | Battery-powered |
| Type of product | Torque screwdriver |

Services

| | |
|-----------------------------------------------------------------------------------------|------------------|
| CalibrationTorque screwdrivers, clockwise / anti-clockwise maximum torque 0,04-20/2 N·m | 020260 0,04-20/2 |
|-----------------------------------------------------------------------------------------|------------------|

Accessories

| | |
|---------------------------------------|-----------|
| Coin-Driver, short Blade length 45 mm | 664311 45 |
|---------------------------------------|-----------|

| | |
|-----------------------------------------------------|------------|
| Alkaline-manganese batteries International size LR3 | 081551 LR3 |
| Coin-Driver Blade length 45 mm | 664310 45 |
| Alkaline-manganese batteries International size LR3 | 081561 LR3 |
| Battery compartment cover Type 1 | 655346 1 |