

**Open ring ratchet plug-in head, Width across flats: 17mm****Order data**

Order number	657920 17
GTIN	4035894038873
Item class	66F

Description**Version:**

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Patented special head for screw fitting pipework connectors and other union nuts.

Advantage:

The **ratchet function saves huge amounts of time and makes work easier** compared to conventional open ring tools.

Cutting dataa:**Legend for drawing and formula:**

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Technical description

Width across flats	17 mm
Height h	16 mm
Plug-in shank	9×12 mm
Width b	45 mm
Pitch S	21 mm
Exchangeable tool	Plug-in head
Ratchet function	yes
Type of product	Ring ratchet plug-in head