



Bit for Pozidriv, 1/4 inch C 6.3 BiTorsion, diamond-coated, Cross-head size / overall length: 2/25mm



Order data

Order number	675530 2/25
GTIN	4013288191649
Item class	63H

Description

Version:

For use in manual drivers or machines with suitable hexagon holder or for use in adapters No. 675000 – 675050.

BiTorsion design with tempered torsion zone to absorb peak loads = longer tool life. Optimum effect when used with BiTorsion quick-change holder No. 675030.

With additional diamond coating of the tips for low ejection forces, lower wear and extended tool life:

Application:

For Phillips cross-head screws to DIN 3128 and DIN ISO 2351-2.

Standard:

DIN ISO 1173.

Material:

Chrome vanadium special alloy, **toughened**.

Technical description

Cross-head size	2
overall length	25 mm
Bit hexagon shank	C 6,3
Manufacturer's designation	855/1 BDC PZ
Standard	DIN ISO 1173
Drive profile	Pozidriv screwdriver

Type of product

Bit tool