

**Milling cutter lock screw through bored, DIN 6367, for mandrel Ø: 32mm****Order data**

Order number	309861 32
GTIN	4250122674207
Item class	30N

Description**Application:**

For attaching shell-type milling cutters.

Coolant supply via lateral holes.

Note:

Compatible with

- **Interface HSK, PSC.**
- **Interface SK and BT only with arbor form ADB.**

Technical description

Thread length	26 mm
Thread M	M16
Head Ø	42 mm
Head thickness	9 mm
for mandrel Ø	32 mm
Standard	DIN 6367

Type of product

Tightening screw