

**Milling cutter lock screw through bored, DIN 6367, for mandrel Ø: 27mm****Order data**

Order number	309861 27
GTIN	4250122674191
Item class	30N

**Description****Application:**

For attaching shell-type milling cutters.  
Coolant supply via lateral holes.

**Note:**

Compatible with

- **Interface HSK, PSC.**
- **Interface SK and BT only with arbor form ADB.**

**Technical description**

for mandrel Ø	27 mm
Thread length	22 mm
Head thickness	8 mm
Head Ø	35 mm
Thread M	M12
Standard	DIN 6367

Type of product

Tightening screw