



## Angled grip wrench



### Order data

Order number	708380
GTIN	4045197895882
Item class	76B

### Description

**Version:**

Long slim jaws, angled 70°. Serrated on the inside; at the rear of the jaws a non-serrated area for clamping hoses. The special head shape ensures that in the clamped condition the handles do not obstruct the working area.

**Application:**

For clamping and gripping in restricted and inaccessible places, where it is essential that the handles do not obstruct the working area.

**Material:**

Jaws of high-quality steel, hardened and tempered.

Head height: 120 mm

Jaw length (serrated area): 60 mm

overall length: 185 mm

Jaw capacity: 60 mm

### Technical description

Head height	120 mm
Jaw length (serrated area)	60 mm
Jaw capacity	60 mm
overall length	185 mm

