



## Ratchet ring plug-in head, Type-Width across flats: 2-16mm



### Order data

Order number	657925 2-16
GTIN	4000896179923
Item class	630

### Description

#### Version:

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Deep cranked **ring ratchet**, reversible. Working angle of 9°.

#### Advantage:

Ratchet operation at extremely inaccessible places.

#### Material:

Chrome vanadium steel, chrome-plated.

#### Cutting dataa:

#### Legend for drawing and formula:

$l_1$  = Lever length without plug-in head

$l_2$  = Adjusted reference dimension on the torque wrench

$l_3$  = Lever length including factory calibration reference dimension

$l_4$  = Reference dimension of the plug-in head

L = Total length of the tool

$T_1$  = Torque to be set

$T_2$  = Specified torque

#### Suitable for:

Torque wrench with rectangular sockets.

#### Note:

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

## Technical description

Plug-in shank	14×18 mm
Width across flats	16 mm
Width b	40 mm
Height h	14.3 mm
Length l	81 mm
Pitch S	36 mm
Exchangeable tool	Plug-in head
Ratchet reversible	yes
Tool with ratchet function	yes
Type of product	Ring ratchet plug-in head