



LED work lamp, Type: 3



Order data

Order number	081415 3
GTIN	4260131238062
Item class	08C

Description

Version:

Powerful, dimmable, long-lived and robust work lamps with **flexible neck** and **sturdy magnetic base**. For connection to a 24 V mains adapter or 24 V machine control system. High-performance LED in an aluminium casing, cold white approx. 5500 Kelvin. Wide beam dispersion angle 120° with uniform illumination.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with 250-V power supply unit.

Note:

Suitable table clamps and magnetic holders can be found under 081418/081419.

Technical description

Magnetic base Ø	66 mm
Illumination	300 lm

Power supply	Mains-powered
Bulb	LED
Weight	550 g
Type of fastening	Magnetic Base
IP Index of Protection	IP 65
Light output	2.5 W
Nominal voltage	250 V
Colour temperature	5500 K
Spread angle	120 degrees
ATEX zone	no
Overall height	620 mm
Light colour	cold white
Lamp head width	30 mm
Lamp head height	15 mm
Lamp head depth	90 mm
Type of product	Desk lamp / workstation lamp

Accessories

Magnetic holder Top mounting plate Ø 95 mm	081419 95
Table clamp Top mounting plate Ø 95 mm	081418 95