



LED work lamp, Type: 7



Order data

Order number	081415 7
GTIN	4260131238055
Item class	08C

Description

Version:

Powerful, long-lived and robust work lamps with **flexible neck** and sturdy **magnetic base**. For connection to a 24V mains adapter or 24V machine control system. High-performance LED in an aluminium casing, cold white approx. 5500 Kelvin. Lamp base with attractive integral switch and dimming function. Wide beam dispersion angle 120° with uniform illumination.

Standard:

Work lights with **flexible neck** and **strong magnetic base**.

- **Dust-proof and splash-proof to IP65.**
- **High-performance LED in an aluminium casing, cold white approx. 5500 Kelvin.**
- **Lamp base with attractive integral switch and dimming function.**

Wide beam dispersion angle 120° with uniform illumination.

Supplied with:

Supplied with power supply unit.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

IP Index of Protection: IP 65

Power consumption: 4.5 W

Illumination: 450 lm

Lamp body height: 600 mm

Magnetic base Ø: 66 mm

Energy efficiency class : A
Weight: 950 g

Technical description

Weight	950 g
Power consumption	4.5 W
Illumination	450 lm
Power supply	Mains-powered
Lamp body height	600 mm
Energy efficiency class	A
IP Index of Protection	IP 65
Magnetic base Ø	66 mm

Accessories

Magnetic holder Top mounting plate Ø 95 mm	081419 95
Table clamp Top mounting plate Ø 95 mm	081418 95