

HOLEX®**Locking C clamp with movable jaws, overall length: 275 mm****Order data**

Order number	709100 275
GTIN	4045197896049
Item class	76B

Description**Version:**

Narrow jaws with high C shape; wide clearance. Sturdy spring steel body. Nickel-plated handles and clamping jaws.

With movable jaws to protect the component.

Application:

Particularly suitable for clamping profiled material with high flanges or bulky components.

Material:

Chrome vanadium steel clamping jaws, drop forged.

Jaw capacity: 75 mm

Technical description

Jaw capacity	75 mm
overall length	275 mm