

Erdi**Ideal snips with 2-component handles small, right-hand cutting, overall length: 230mm**

Order data

Order number	764000 230
GTIN	4010220024720
Item class	73X

Description

Version:

Drop-forged head; blades induction hardened. Double compound action with integral return spring. Handles of sheet metal, nickel-plated. 2-component handle with non-slip insert of soft material, easy on the hand.

Snip jaws of stainless steel (HRC 60), serrated cutters.

Cutting power: Sheet metal up to 1.2 mm, stainless steel sheet up to 1.0 mm.

Application:

For continuous straight and shaped cutting.

Technical description

Length cutter	27 mm
overall length	230 mm
Application type	right-hand cutting
Type of product	Scissors

Accessories

Repair kit for Ideal snips	764010
----------------------------	--------