

**Erdi****Ideal snips with 2-component handles very small, right-hand cutting, overall length: 180mm**

## Order data

Order number	764050 180
GTIN	4010220031308
Item class	73X

## Description

**Version:**

Drop-forged head; blades induction hardened. Double compound action with integral return spring. Handles of sheet metal, nickel-plated. 2-component handle with non-slip insert of soft material, easy on the hand.

Snip jaws of high quality steel-S (HRC 60 – 62), **25 % less force required.**

**Cutting power:** Sheet metal up to 1.2 mm, stainless steel sheet up to 1.0 mm.

**Application:**

For continuous straight and shaped cutting.

For very tight radii and places where access is difficult.

## Technical description

Length cutter	20 mm
overall length	180 mm
Application type	right-hand cutting
Type of product	Scissors