

HOLEX®
Pipe welder's clamp, overall length: 280 mm

Order data

Order number	709500 280
GTIN	4045197896087
Item class	76B

Description
Version:

U-shaped clamping jaws, the upper jaws have Vee profile to give secure three-point contact when clamping pipes. Sturdy spring steel body. Fully nickel-plated.

Application:

For centralised clamping of pipes and rods when welding.

Material:

Chrome vanadium steel clamping jaws.

Spare part:

Spare spring No. 708300 size 250.

Jaw capacity for pipes: 10 - 90 mm

Jaw capacity for pipes: 2/5-3.1/2 inch

Technical description

Jaw capacity for pipes	10 - 90 mm
Jaw capacity for pipes	2/5-3.1/2 inch
overall length	280 mm
upper gripper jaw	Vee-form
Type of jaws	U-shape - Vee-form
Support	Three-point support
Material of pliers	Spring steel
Material of gripper jaws	Chrome vanadium steel

Surface

nickel-plated