

HOLEX®**Sheet metal clamp, overall length: 180 mm****Order data**

Order number	709700 180
GTIN	4045197896094
Item class	76B

Description**Version:**

Particularly wide and flat clamping jaws. Sturdy spring steel body. Fully nickel-plated.

Application:

Particularly suitable for holding, bending, and flanging sheet metal.

Material:

Chrome vanadium steel clamping jaws.

Spare part:

Spare spring No. 708300 size 175.

Jaw width: 80 mm

Jaw capacity: 45 mm

Technical description

Jaw width	80 mm
Jaw capacity	45 mm
overall length	180 mm