

**6 mm blade Slot-head, Blade width: 5,5mm****Order data**

Order number	659928 5,5
GTIN	7610733225125
Item class	63D

Description**Version:**

Blade of chrome vanadium special alloy combining maximum hardness and exceptional toughness. Surface nickel-plated and chrome-plated, black tip.

Suitable for:

Torque screwdriver No. 659906 (up to Cat. 53) / 659908 (up to Cat. 53) / 659911 size 80; 250; 500 (up to Cat. 48) / 659912 **size 200; 500** / 659918 / 659956 size 200; 500 / 659957 size 200; 500 / 659958 size 200; 500 and assembly screwdriver sets No. 625441 / 667532 / 667551 / 667601 / 667615.

Technical description

Drive profile	Slot-head screwdriver
Blade designation	3
overall length	180 mm
Blade width	5.5 mm
Usable length	100 mm
Cutter thickness	0.8 mm
Type of product	Screwdriver bit