

Garant**Snipe nose pliers, straight, chrome-plated, with grips, overall length: 200mm**

Order data

Order number	713040 200
GTIN	4045197373564
Item class	71B

Description

Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Standard:**DIN ISO 5745****Material:**

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	200 mm
Jaw length	73 mm
Handle	Multi-component covering with non-slip Haptoprene surface
Jaw design	snipe-nosed, straight
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Material	Chromium vanadium steel

Surface	chrome-plated
Type of product	Multi-function pliers