

**Snipe nose pliers, straight, chrome-plated, with grips, overall length: 125mm****Order data**

Order number	713100 125
GTIN	4003773043065
Item class	73F

Description**Version:**

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Jaws chrome-plated. Twist-tolerant flexible precision tips. Plastic coated handles.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	125 mm
Jaw length	27 mm
Handle	plastic coated
Jaw design	snipe-nosed, straight
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Material	Chromium vanadium steel

Surface	chrome-plated
Type of product	Multi-function pliers