



## Stepped drill bit, Drill step range: 4-20mm



### Order data

Order number	676305 4-20
GTIN	4013288119155
Item class	63H

### Description

#### Version:

1/4 inch hexagon shank to DIN 3126 C 6.3.

9 drill steps **2 mm** increments, for use in materials up to 4 mm thickness. With edge breaker (sheet deburrer) at  $\varnothing$  10 for 1 mm sheet metals.

#### Advantage:

Quick and uncomplicated changes between drill, countersink, and screw bits.

#### Application:

Ideal for repair and assembly work in mobile situations.

### Technical description

Drill step range	4 - 20 mm
Number of drill steps	9
Shaft length	20 mm
maximum sheet thickness	4 mm
Step height	4 mm
overall length	67 mm
Pitch	2 mm
Bit hexagon shank	C 6,3
Manufacturer's designation	843
Tool material	HSS

Type of product

Stepped drill bit