



## Snipe nose pliers, straight, chrome-plated, with grips, overall length: 160mm



### Order data

Order number	713100 160
GTIN	4003773022817
Item class	73F

### Description

#### Version:

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Jaws chrome-plated. Twist-tolerant flexible precision tips. Handles with multi-component coverings.

#### Standard:

**DIN ISO 5745**

#### Material:

Chrome vanadium steel, drop-forged and oil-hardened.

### Technical description

overall length	160 mm
Jaw length	50 mm
Handle	Multi-component covering
Jaw design	snipe-nosed, straight
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Material	Chromium vanadium steel

Surface	chrome-plated
Type of product	Multi-function pliers