

**HSS jobber drill bit, Drill Ø: 5mm****Order data**

| | |
|--------------|---------------|
| Order number | 676302 5 |
| GTIN | 4013288118745 |
| Item class | 63H |

Description**Version:**

1/4 inch hexagon shank to DIN 3126 C 6.3.

Advantage:

Quick, uncomplicated changes between drill, countersink, and screw bits.

Application:

Ideal for repair and assembly work in mobile situations.

General purpose use in metal, wood and plastic.

Special rivet hole sizes 3.1 and 5.1 mm.

Technical description

| | |
|----------------------------|------------------|
| Flute length | 26 mm |
| overall length | 50 mm |
| Drill Ø | 5 mm |
| Shaft length | 14 mm |
| Bit hexagon shank | C 6,3 |
| Manufacturer's designation | 848 HSS |
| Tool material | HSS |
| Point angle | 118 degrees |
| Type of product | Jobber drill bit |

