



## HSS combination tap bit, for threads: M3



### Order data

Order number	676306 M3
GTIN	4013288119032
Item class	63H

### Description

#### Version:

1/4 inch hexagon shank to DIN 3126 C 6.3.

#### Advantage:

Quick and uncomplicated changes between drill, countersink, and screw bits.

#### Application:

Ideal for repair and assembly work in mobile situations.

#### 1 tool for 3 operations:

drill tapping hole – tap thread – deburr / countersink.

**For use in power drills with forward and reverse drive.**

### Technical description

Drill length a	5 mm
Twist drill Ø	2.5 mm
Pitch	0.5 mm
overall length	36 mm
Shaft length	12 mm
for threads	M3
Manufacturer's designation	847 HSS
Thread type	M
Tool material	HSS
Point angle	60 degrees

Tolerance class	ISO 2 6H
Flank angle	60 degrees
Application for type of drilling	up to 1×D for through holes
Bit hexagon shank	C 6,3
Type of product	Tap bit