

**HSS jobber drill bit, Drill Ø: 6,8mm****Order data**

Order number	676302 6,8
GTIN	4013288118912
Item class	63H

Description**Version:**

1/4 inch hexagon shank to DIN 3126 C 6.3.

Advantage:

Quick, uncomplicated changes between drill, countersink, and screw bits.

Application:

Ideal for repair and assembly work in mobile situations.

General purpose use in metal, wood and plastic.

Special rivet hole sizes 3.1 and 5.1 mm.

Technical description

Flute length	30 mm
overall length	50 mm
Shaft length	14 mm
Drill Ø	6.8 mm
Bit hexagon shank	C 6,3
Manufacturer's designation	848 HSS
Tool material	HSS
Point angle	118 degrees
Type of product	Jobber drill bit

