

**Jobber drill bit, for wood, Drill Ø: 10mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 676315 10     |
| GTIN         | 9002696296447 |
| Item class   | 66B           |

**Description****Version:**

1/4 inch hexagon shank to DIN 3126 C 6.3.

**Advantage:**

Quick and uncomplicated changes between drill, countersink, and screw bits.

**Application:**

Ideal for repair and assembly work in mobile situations.

For drilling smooth and accurate blind holes in softwood, hardwood, and faced boards.

**Technical description**

|                   |                  |
|-------------------|------------------|
| Flute length      | 70 mm            |
| overall length    | 110 mm           |
| Drill Ø           | 10 mm            |
| Bit hexagon shank | E 6,3            |
| Tool material     | HSS              |
| Type of product   | Jobber drill bit |