



## HSS combination tap bit, for threads: M8



### Order data

Order number	676306 M8
GTIN	4013288118936
Item class	63H

### Description

**Version:**

1/4 inch hexagon shank to DIN 3126 C 6.3.

**Advantage:**

Quick and uncomplicated changes between drill, countersink, and screw bits.

**Application:**

Ideal for repair and assembly work in mobile situations.

**1 tool for 3 operations:**

drill tapping hole – tap thread – deburr / countersink.

**For use in power drills with forward and reverse drive.**

### Technical description

Twist drill Ø	6.8 mm
Pitch	1.25 mm
for threads	M8
Drill length a	11 mm
overall length	51 mm
Shaft length	12 mm
Manufacturer's designation	847 HSS
Thread type	M
Tool material	HSS
Point angle	60 degrees

Tolerance class	ISO 2 6H
Flank angle	60 degrees
Application for type of drilling	up to 1×D for through holes
Bit hexagon shank	C 6,3
Type of product	Tap bit