



Countersinking bit set in a sturdy box, 8 pieces



Order data

| | |
|--------------|---------------|
| Order number | 676312 |
| GTIN | 4013288101587 |
| Item class | 63H |

Description

Version:

1/4 inch hexagon shank to DIN 3126 C 6.3.

Advantage:

Quick and uncomplicated changes between drill, countersink, and screw bits.

Application:

Ideal for repair and assembly work in mobile situations.

Content:

Countersinking bits, three-flute: No. 676310 1 pc. each size 6.3; 8.3; 10.4; 12.4; 16.5; 20.5

Screwdriver holder: 1 pc. No. 676410

„Rapidaptor“ coupling shank: 1 pc. similar to No. 675020 size 6.3K (without magnet)

Technical description

| | |
|---------------------------|------------|
| Number of countersinks | 6 |
| Number of cutting edges Z | 3 |
| Number of pieces | 8 |
| Countersink tip angle | 90 degrees |

| | |
|-----------------|-------------------------------|
| Tool material | HSS |
| Standard | DIN 335 C |
| Type of product | Stepped drill and countersink |

Accessories

| | |
|--|-------------|
| Shank with magnet / quick-change coupling Hexagon shank 6,3K | 675020 6,3K |
| Countersinking bit, three-flute External Ø 20,5 mm | 676310 20,5 |
| Countersinking bit, three-flute External Ø 6,3 mm | 676310 6,3 |
| Countersinking bit, three-flute External Ø 16,5 mm | 676310 16,5 |
| Countersinking bit, three-flute External Ø 8,3 mm | 676310 8,3 |
| Countersinking bit, three-flute External Ø 12,4 mm | 676310 12,4 |
| Countersinking bit, three-flute External Ø 10,4 mm | 676310 10,4 |