



## Bits set with drive tool 32 pieces, Type: M



### Order data

Order number	676100 M
GTIN	4013288157027
Item class	63H

### Description

#### Version:

Practical Kraftform Kompakt® set of bits and drive tool **for manual and machine drives**.  
**Kraftform** handle with quick-change holder for 1/4 inch bits with C 6.3 and E 6.3 shank.

#### Application:

Popular standard profiles for standard screw connections.

#### Content:

Bits, length 25 mm, C 6.3, for Phillips: No. 675200 3 pcs. each size 1/25; 2/25; 3/25

Bits, length 25 mm, C 6.3, for Pozidriv: No. 675220 3 pcs. each size 1/25; 2/25; 3/25

Bits, length 25 mm, C 6.3, for hex socket: No. 675240 1 pc. each size 4; 5; 6

Bits, length 25 mm, C 6.3, for internal Torx® with pin: No. 675350 1 pc. each size TX10; TX15; TX20; TX25; TX30; TX40

Bits, length 25 mm, C 6.3, for slot-head: 1 pc. each size 0.6x4.5; 1.0x5.5; 1.2x6.5

Screwdriver handle: 1 pc. No. 676410 with „Rapidaptor“ quick-change chuck C/E 6.3

„Rapidaptor“ coupling shank: 1 pc. No. 675020 size 6.3K

### Technical description

Drive profile	Slot-head screwdriver
---------------	-----------------------

Drive profile	Screwdriver for TORX® screws with hole
Drive profile	Hexagon screwdriver
Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver
Manufacturer's designation	KK 70 Allround
Number of pieces	32
Drive tool	Screwdriver handle
telescopic blade is retractable into the handle	no
Type of product	Bit tool

## Accessories

Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 1/25 mm	675220 1/25
Bit for Torx®, 1/4 inch C 6.3with bore Torx® profile TX25	675350 TX25
Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 2/25 mm	675200 2/25
Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 3/25 mm	675200 3/25
Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 2/25 mm	675220 2/25
Kraftform screwdriver holder for 1/4 inch bits C 6.3 and E 6.3with quick-change chuck Hexagon socket 6,3 mm	676410 6,3
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 4 mm	675240 4
Bit for Phillips, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 1/25 mm	675200 1/25
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 5 mm	675240 5
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 6 mm	675240 6

Bit for Torx®, 1/4 inch C 6.3with bore Torx® profile TX30	675350 TX30
Bit for Torx®, 1/4 inch C 6.3with bore Torx® profile TX15	675350 TX15
Bit for Pozidriv, 1/4 inch C 6.3, with torsion zone Cross-head size / overall length 3/25 mm	675220 3/25
Bit for Torx®, 1/4 inch C 6.3with bore Torx® profile TX20	675350 TX20
Bit for Torx®, 1/4 inch C 6.3with bore Torx® profile TX40	675350 TX40
Bit for Torx®, 1/4 inch C 6.3with bore Torx® profile TX10	675350 TX10
Shank with magnet / quick-change coupling Hexagon shank 6,3K	675020 6,3K