

**HSS jobber drill bit, Drill Ø: 8,5mm****Order data**

Order number	676302 8,5
GTIN	4013288118882
Item class	63H

**Description****Version:**

1/4 inch hexagon shank to DIN 3126 C 6.3.

**Advantage:**

Quick, uncomplicated changes between drill, countersink, and screw bits.

**Application:**

Ideal for repair and assembly work in mobile situations.

General purpose use in metal, wood and plastic.

Special rivet hole sizes 3.1 and 5.1 mm.

**Technical description**

Drill Ø	8.5 mm
overall length	53 mm
Flute length	33 mm
Shaft length	14 mm
Bit hexagon shank	C 6,3
Manufacturer's designation	848 HSS
Tool material	HSS
Point angle	118 degrees
Type of product	Jobber drill bit

