

**Snipe nose pliers, angled, bright finished, overall length: 160mm****Order data**

Order number	713600 160
GTIN	4045197283566
Item class	72B

Description**Version:**

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Jaws bright finished, plastic coated handles.

Standard:

DIN ISO 5745

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	160 mm
Jaw length	50 mm
Jaw design	snipe-nosed, angled (40° – 45°)
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Handle	plastic coated
Material	Chrome vanadium steel, drop-forged and oil-hardened
Surface	bright finish

Type of product

Multi-function pliers