

**Snipe nose pliers, straight, bright finished, overall length: 160mm****Order data**

Order number	713200 160
GTIN	4045197166036
Item class	72B

**Description****Version:**

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Jaws bright finished, plastic coated handles.

**Standard:**

**DIN ISO 5745**

**Material:**

Chrome vanadium steel, drop-forged and oil-hardened.

**Technical description**

overall length	160 mm
Jaw length	50 mm
Handle	plastic coated
Jaw design	snipe-nosed, straight
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Material	Chromium vanadium steel
Surface	bright finish

Type of product

Multi-function pliers