

**Erdi****Ideal snips with 2-component handles, right-hand cutting, overall length: 260mm**

## Order data

Order number	766000 260
GTIN	4010220019283
Item class	73X

## Description

**Version:**

Drop-forged head, blades induction hardened. Adjustable pivot pins, double leverage with integrated return spring.

Ultra-fine serrated. Snip jaws made of **stainless steel** (HRC 58 – 60), handles of steel plate, nickel plated. 2-component handle with non-slip insert of soft material, easy on the hand.

**Cutting capacity:** Sheet metal up to 1.8 mm, stainless steel up to 1.2mm.

**Application:**

For continuous straight and shaped cutting.

## Technical description

Length cutter	33 mm
overall length	260 mm
Application type	right-hand cutting
Type of product	Scissors

## Accessories

Repair kit for Ideal snips	766020
----------------------------	--------