

Erdi**Ideal snips with HSS blades, left-hand cutting, overall length: 260mm**

Order data

Order number	766360 260
GTIN	4010220000281
Item class	73X

Description

Version:

Drop-forged head, blades induction hardened. Adjustable pivot pins, double leverage with integrated return spring.

Snip jaws with **HSS blades** (HRC 65). Particularly long blade service life. Handles of sheet steel, nickel-plated. 2-component handle with non-slip insert of soft material, easy on the hand.

Cutting capacity: Metal sheets up to 1.8 mm, stainless steel sheets up to 1.2 mm.

Application:

For continuous straight and shaped cutting.

Technical description

overall length	260 mm
Length cutter	33 mm
Application type	left-hand cutting
Type of product	Scissors

Accessories

Repair kit for Ideal snips	766020
----------------------------	--------