

**ERGO™ snipe nose pliers, straight, chrome-plated, overall length: 200mm****Order data**

Order number	713940 200
GTIN	7314150102174
Item class	730

**Description****Version:**

Chrome vanadium steel, chrome-plated head and joint. Exceptionally slim, serrated snipe nose jaws. Heavy-duty grips with **opening spring that can be engaged / disengaged**. Induction hardened cutting edges (approx. 59 HRC); suitable for hard and soft wire.

**Standard:**

**DIN ISO 5745**

**Technical description**

overall length	200 mm
Jaw length	72 mm
Handle	Heavy-duty ERGO® grip
with selectable return spring	yes
Jaw design	snipe-nosed, straight
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 59 HRC)
Type of jaws	inner face roughened
Material	Chrome vanadium steel
Surface	chrome-plated

Type of product

Multi-function pliers