



Snipe nose pliers, offset VDE insulated, overall length: 220mm



Order data

Order number	713380 220
GTIN	4007582014766
Item class	76B

Description

Version:

Cutting edges induction hardened (approx. 64 HRC); suitable even for piano wire. Long snipe nose jaws with "WAVE profile" for gripping delicate parts such as cables or threaded rods. Inner face of jaws serrated near the tip. Handles with thick-walled grips **insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.**

Application:

Ideal for electrical installation work - offset design for improved ergonomics and a clear view of the working area.

Material:

Special tool steel, jaws bright finished. Handles with multi-component coverings.

Technical description

overall length	220 mm
Jaw length	65 mm
Jaw design	snipe-nosed, cranked
Standard	DIN EN IEC 60900 / VDE 0682-201
Jaw characteristics	Induction hardened precision cutting edges (approx. 64 HRC)
Type of jaws	inner face serrated
Handle	Multi-component covering

Material	Special tool steel
Surface	bright finish
Type of product	Multi-function pliers