

**HOLEX®****Ideal snips with 2-component handles, right-hand, overall length: 260 mm**

## Order data

Order number	766040 260
GTIN	4045197166937
Item class	72D

## Description

**Version:**

Cutter head drop forged, blades induction hardened. Adjustable pivot pins, double leverage with integrated return spring.

Ultra-fine serrated. Snip jaws made of **stainless steel** (HRC 58 – 60), handles of steel plate, nickel plated. 2-component handle with non-slip insert of soft material, easy on the hand.

**Cutting capacity:** Sheet metal up to 1.8 mm, stainless steel up to 1.2mm.

**Application:**

For continuous straight and shaped cutting.

Length cutter: 33 mm

## Technical description

overall length	260 mm
Length cutter	33 mm
Application type	right-hand