

Garant**Snipe nose pliers, angled, chrome-plated, with grips, overall length: 160mm****Order data**

Order number	713440 160
GTIN	4045197373588
Item class	71B

Description**Version:**

Very long snipe nose jaws. Cutting edges induction hardened (approx. 61 HRC), suitable for hard and soft wire. Serrated inside jaws.

Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Standard:**DIN ISO 5745****Material:**

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

overall length	160 mm
Jaw length	50 mm
Jaw design	snipe-nosed, angled (40° – 45°)
Standard	DIN ISO 5745
Jaw characteristics	Cutting edges induction hardened (approx. 60 HRC)
Type of jaws	inner face roughened
Handle	Multi-component covering with non-slip Haptoprene surface

Material	Chrome vanadium steel, drop-forged and oil-hardened
Surface	chrome-plated
Type of product	Multi-function pliers